

セラミック培養栓

製品名	A 上部外径	B 差込口径	C 差込上部径	D 全体高さ	E セラミックサイズ	製品名2
TEC-10	14	7	10	36	$9\pi \times 7t$	TEC-10
TEC-12	16	9	12	36	$9\pi \times 7t$	TEC-12
TEC-15	19	12	15	36	$9\pi \times 7t$	TEC-15
TEC-17	22	13	17	46	$15\pi \times 7t$	TEC-17
TEC-19	24	15	19	46	$15\pi \times 7t$	TEC-19
TEC-22	27	18	22	46	$15\pi \times 7t$	TEC-22
TEC-24	29	20	24	58	$15\pi \times 7t$	TEC-24
TEC-28	34	21	28	58	$21\pi \times 9t$	TEC-28
TEC-32	38	22	32	63	$21\pi \times 9t$	TEC-32
TEC-38	44	26	38	88	$31\pi \times 11t$	TEC-38
TEC-42	48	30	42	88	$31\pi \times 11t$	TEC-42

